

CAT. N° 0 365 71


**VENTILATOR WITH METAL LOUVRE - IP32 - IK10 - 30/160 M
?/H - RAL 7032**

Unit price ex. taxes	€98.07
Pack (number of units)	1
Volume (dm ³)	2,006
Weight (g)	1 058,00

Product characteristics
Ventilators with metal louver

- IP 32 - IK 10
- Ventilator is mounted on the outside of the enclosure or cabinet
- A second outlet can be installed to increase the flow rate and optimise discharge rates from the enclosure
- 230 V - 50/60 Hz

30/160 m³/h

- 30 m³ installed with filter
- 160 m³ for free blow-out
- Supplied with a pair of metal louvres, a pair of anti-insect grilles and an internal finger-guard grille
- Beige RAL 7032

General characteristics
**Heat regulation for cabinets and enclosures -
ventilators**
Documentation

Catalogue pages & additional information

- [Description page \(p.312\)](#)
- [Heat regulation for cabinets and enclosures](#)


Installation instructions & related documents

- [041570/01](#)