

19" LED Monitor

Art. no. TVAC10021

Page 1 of 2



- Resolution: 1280 × 1024 pixels
- Fast response time (5 ms)
- LED background illumination: Superior colour display and contrast
- Graphical on-screen display (OSD)
- Connections: HDMI, VGA, 2 × BNC, cinch (audio), PC audio
- Integrated loudspeakers
- Low power consumption (LED technology)
- For wall and ceiling installation (with VESA mount)

The 19" LED monitor offers outstanding picture quality and fast reaction times for optimum picture fidelity. The integrated BNC connections and other interfaces equip the monitor with requirements for professional video surveillance. The signal is detected automatically, all settings can easily be made in the on-screen display in several languages. Thanks to energy-saving LED technology, the monitor has a low power consumption – and can be used efficiently for 24/7 operation.

Detailed surveillance pictures

With its high resolution, outstanding picture fidelity and fast reaction time, the monitor produces accurate surveillance pictures. The LED backlighting ensures optimum contrast and an extremely realistic color display.

Versatile connections

The video inputs as HDMI, VGA and BNC offer flexibility for connecting the monitor to a recorder, live-cameras or a computer. Integrated loudspeaker and audio inputs also allow soundtracks to be played. Therefore the monitor is a cost-effective component for versatile surveillance and IT systems.

Efficient uninterrupted 24/7 use

Thanks to high-quality industry components, the monitor is suitable for uninterrupted 24/7 use. The energy-efficient LED display ensures very low power consumption.

Easy installation

VESA standard mounts can be used to fix it to a wall or ceiling. This makes installation fast and easy.

19" LED Monitor

Art. no. TVAC10021

Page 2 of 2

Technical Data:

Dimensions	417 x 341 x 64 mm
Connections	1 x HDMI, 1 x VGA, 2 x BNC, 1 x audio (3.5 mm jack), 2 x chinch audio, 1 x BNC-Out
Output	1 x BNC
Horizontal/vertical viewing angle	170° x 160° °
Picture format	4:3
Screen diagonal	19 "
Width	417 mm
Gross weight	4.6 kg
Display surface	matte
EAN	4043158053548
Input	1 x HDMI, 1 x VGA, 2 x BNC, 1 x audio (3.5mm jack), 2 x chinch audio
Color levels	16.7 MIO
Frequency range	30 – 80KHz (H) / 50 – 75Hz (V) GHz
Housing material	Plastic
Brightness	250 cd/m ²
Height	341 mm
Comb filter	3D

Contrast ratio	1.000:1
Loudspeaker	2 x 2,5 W
Power consumption	max. 25 W W
Max. operating temperature	40 °C
Max. humidity	max. 70 %
Min. operating temperature	0 °C
Monitor type	LED
Net weight	4.1 kg
Pixel pitch	0.294 x 0.294 (H) x (V) mm
Reaction time	5 ms
Signal detection	Automatic
DC voltage supply	12 V
Power consumption	3.000 mA
Video system	PAL / NTSC