


filter regulator MS4-LFR-1/4-D6-CRV-AS

Part number: 529146

★ Core product range

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | 4 |
| Series | MS |
| Actuator lock | Rotary knob with lock with accessories, lockable |
| Assembly position | Vertical +/- 5° |
| Grade of filtration | 5 µm |
| Condensate drain | fully automatic |
| Design structure | Filter regulator with pressure gauge |
| Max. condensate volume | 19 ml |
| Controller function | Output pressure constant with secondary exhaust with return flow |
| Bowl guard | Plastic guard |
| Pressure gauge | with pressure gauge |
| Operating pressure | 2 ... 12 bar |
| Pressure regulation range | 0.3 ... 7 bar |
| Max. pressure hysteresis | 0.25 bar |
| Standard nominal flow rate | 1,500 l/min |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:-] Inert gases |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Storage temperature | -10 ... 60 °C |
| Air purity class at output | Compressed air in accordance with ISO8573-1:2010 [6:4:4] |
| Medium temperature | 5 ... 60 °C |
| Ambient temperature | 5 ... 60 °C |
| Product weight | 275 g |
| Mounting type | Optional Front panel installation Line installation with accessories |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 2 | G1/4 |
| Materials note | Conforms to RoHS |
| Material of connecting plate | Aluminium die cast |
| Material control panel | PA POM |
| Material seals | NBR |
| Material filter | PE |
| Material housing | Aluminium die cast |
| Material membrane | NBR |
| Material bowl | PC |
| Material separating plate | POM |