

Features

- Panel Mounted
- Solder Tags
- Nylon body

RS PRO 6.35mm Mono Jack Socket

RS Stock No.: 0588685



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Jack Sockets



Product Description

This 6.35mm mono jack socket has a robust nylon body and Nickel Silver contacts. It has a metal front nut, white bezel and 2 fibre washers for panel fixing.

"Jack Sockets are often used in musical instruments, found on amplifiers and electric guitars, keyboards and drum kits. Whether in a professional studio or stage environment, or for home use, jack connectors are a staple connector for musicians and engineers. They also have applications in commercial public address systems and industrial systems.

General Specifications

Gender	Female
Size	6.35mm
Colour	Black

Mechanical Specifications

Max. Panel Thickness	4.3mm
Termination method	Solder tags
Body moulding	PA66 Nylon
Contacts	Nickel Silver plated

Electrical Specifications

Maximum Current	5A
Dielectric Withstand Voltage	2000V DC Min
Nominal Contact Resistance	<50mΩ
Life (minimum)	10,000+ operations
Temperature Rating	-10°C to +70°C

Approvals

Standards Met	RoHS

Jack Sockets



