

FER10018F-H



Bootlace Ferrule 10SQMM 18 long



General Information

Extended Product Type	FER10018F-H
Product ID	7TBA301140R0092
EAN	5415022401066
Catalog Description	Bootlace Ferrule 10SQMM 18 long
Long Description	Polypropylene-Insulated Bootlace Ferrule, Wire Size 10mm ² , 18mm, Copper, Tin Plated, Temperature Range -30 to 105 Degrees C, 600V Max, French Color Brown

Ordering

EAN	5415022401066
Minimum Order Quantity	12500 piece
Customs Tariff Number	8536908585

Dimensions

Product Net Weight	0.907 g
--------------------	---------

Container Information

Package Level 1 Width	25.4 mm
Package Level 1 Height	101.6 mm
Package Level 1 Depth / Length	152.4 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	152.4 mm
Package Level 2 Height	88.9 mm
Package Level 2 Depth / Length	177.8 mm
Package Level 3 Units	5000 piece
Package Level 3 Width	317.5 mm
Package Level 3 Height	203.2 mm
Package Level 3 Depth / Length	482.6 mm

Additional Information

Brand / Label	Spec-Kon
Color	Brown - French
Material	Copper

Product Main Type	COMPRESSION TERMINALS
Product Name	ELECTRICAL WIRING TERMINAL
Product Type	Polypropylene-Insulated Bootlace Ferrule
UPC	786210135748

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	FER10018F-H
Instructions and Manuals	FER10018F-H

Classifications

ETIM 6	EC000005 - Cable end sleeve
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

