

## Hose holder with cover - WP-BASE C PA HF 15,8 BK - 3240960

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Hose holder with cover

Image shows WP-TCC PA HF 10.0 BK version



### Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 50 pc                                                                                                   |
| Minimum order quantity               | 50 pc                                                                                                   |
| GTIN                                 | <br>4 046356 710671 |
| Weight per Piece (excluding packing) | 4.51 g                                                                                                  |
| Custom tariff number                 | 39174000                                                                                                |
| Country of origin                    | Germany                                                                                                 |

### Technical data

#### Dimensions

|               |         |
|---------------|---------|
| Hole diameter | 5.5 mm  |
| Diameter      | 15.8 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 115 °C |
|---------------------------------|-------------------|

#### General

|                                         |              |
|-----------------------------------------|--------------|
| Color                                   | black        |
| Components                              | Halogen-free |
| Inflammability class according to UL 94 | V0           |
| Material                                | PA           |

# Hose holder with cover - WP-BASE C PA HF 15,8 BK - 3240960

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141131 |
| eCl@ss 4.1 | 27141131 |
| eCl@ss 5.0 | 27141131 |
| eCl@ss 5.1 | 27141120 |
| eCl@ss 6.0 | 27141120 |
| eCl@ss 7.0 | 27141120 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC000127 |
| ETIM 5.0 | EC001171 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 39121411 |

## Approvals

### Approvals

---

#### Approvals

UL Recognized

---


#### Ex Approvals

---

Approvals submitted

---

### Approval details



## Accessories

Accessories

Corrugated pipe

## Hose holder with cover - WP-BASE C PA HF 15,8 BK - 3240960

### Accessories

Protective hose - WP-PA HF 15,8 BK - 3240682



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

---

Protective hose - WP-PA HF-HB 15,8 BK - 3240840



Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

---

---