



CWT2-R

SOLDERSLEEVE WIRE SPLICE RED, OD MAX=2.8mm, 0.6-2.0mm² (AWG 22-18)

Product Properties:

Colour	Red
Operating temperature	-55-125 °C
Voltage max	600V
Connector type	Lödskarvhylsa, dubbelring

Dimensions:

MOQ	50 .
Unit	pcs
Nominal cross section	0.6-2 mm ²

Approvals:

Compliance:

Conflict Minerals	Yes, see report under tab "Documents"
Iron and Steel Sanction	Compliance
Link to manufacturer COC	https://www.te.com/commerce/alt/SinglePartSearch.do?PN=747081-000
REACH	Yes. CAS 7439-92-1, 32 %, CAS 7440-43-9, 18 %
RoHS	No
SCIP	9edec777-e6c2-4a86-b7cd-5079b95b83ef
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000466 - Heat-shrink crimp connection
ETIM-Release	9.0
Trademark	TE Connectivity

Product Group	Soldersleeve wire splices
Search Description	747081-000, B-008-13
Alternative SKU	CWT2-R

Logistic information:

Barcode	733117640020
Country of origin	MX
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	50 .
Stock code	CWT2-R
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.