

Datasheet

RS Pro Round Fixed Height Feet, PD.2115BL 11.1mm, PUR, +65°C -34°C

RS Stock No: **248-546**



Product Details

RS Pro round anti-vibration feet in black colour, is made with PUR for long life durability. It has a diameter of 11.1 mm and overall height of 5 mm. It features excellent skid resistance with a high coefficient of friction and excellent resistance to moving and staining. It has a temperature rating of -34 to +65°C. This flexible polyurethane feet is suitable for indoor and limited outdoor applications.

Features and Benefits

- Long ageing resiliency and will not crack or harden
- Ideal for use on glass, aluminium, stainless steel, acrylic plastic, polyethylene, polystyrene, ABS, polypropylene and polycarbonate
- To ensure maximum adhesion, surfaces must be clean, dry and well unified
- Flexible polyurethane feet suitable for indoor and limited outdoor applications

**Specifications:**

Foot Colour	Black
Foot Shape	Round
Material	PUR
Mounting Type	Adhesive
Type	Feet
Diameter	11.1 mm
Maximum Operating Temperature	+65°C
Minimum Operating Temperature	-34°C
Overall Height	5 mm
Finish	Gloss
Hardness	65 to 70 Shore A