

Technical data sheet

Article number:
924-00444

QDF2-6F90

Product Group	90° Nylon Flag Quick Connect Fully Insulated Female Funnel Entry 105 °C
Product Family	Double Grip Pre-Insulated Terminals
Material	Brass (BS), Polyamide 6.6 (PA66)
Colour	Blue (BU)
Application Range	Low Voltage
Conductor Size Range mm²	1.5-2.5 mm ²
Diameter (D)	2.3 mm
Halogen-free	Yes
Length (L)	16.1 mm
Length (L3)	7.9 mm
Max Current	27 A
Max Voltage	600 V
Operating Temperature	+105 °C
Package Content	50 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	6.6 mm

HF ✓

RoHS ✓