

Features

- Delivers smooth, effortless flush cuts in both wood and metal.
- Made from a standard 0.9mm gauge M2 High Speed Steel, it is designed for cutting soft nails, mild steel, and non-ferrous metal components embedded in wood.
- With its balanced gauge and length, this blade offers excellent flexible, flush-cutting capability for versatile on-site applications.

Reciprocating Saw Blade –Wood & Metal 225 x 19 x 0.9mm –Fast Cut

RS Stock No.: 0757833



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Reciprocating Saw Blade

0757833 Wood and Metal Reciprocating Saw Blade delivers smooth, effortless flush cuts in both wood and metal. Made from a standard 0.9mm gauge High Speed Steel, it is designed for cutting soft nails, mild steel, and non-ferrous metal components embedded in wood. With its balanced gauge and length, this blade offers excellent flexible, flush-cutting capability for versatile on-site applications.

- *Manufactured with D6A Shock-Resisting Tool Steel & M2 High Speed Steel Teeth*
- *Universal Fitting, compatible with all S-shank 1/2" Reciprocating Saws*
- *Suitable for use on Sheet Metal, Wood With Nails, Wooden Pallets & Pipes*
- *Supplied in 5pc Packs*

General Specifications

Tooth Design	Side Set, Milled
Type	Reciprocating Saw Blade
Teeth Spacing	1.8mm - 2.5mm
TPI	10-14
Thickness	1.25mm
Max Cut Depth	175mm
Cut Type	Fast Cutting
Blade Material	M2 High Speed Steel
Body Material	D6A Shock-Resisting Tool Steel
Fitting	S-Shank 1/2"
Length	225mm
Width	19mm

Stock No.	Cut Type	Thickness	Length	Width
XXX-XXXX 0757831	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757832	Coarse Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757833	Fast Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757834	Fine Cutting	0.9mm	150mm	19mm

Approvals

Declarations	REACH DoC
---------------------	-----------

Similar Products

Stock No.	Brand	Product Name	Cut Type	Thickness	Length	Width
XXX-XXXX 0757831	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757832	RS PRO	Reciprocating Saw Blade	Coarse Cutting	1.25mm	225mm	19mm
XXX-XXXX 0757833	RS PRO	Reciprocating Saw Blade	Fast Cutting	1.25mm	225mm	19mm
XXX-XXXX 0757834	RS PRO	Reciprocating Saw Blade	Coarse Cutting	1.25mm	300mm	19mm

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories