



Product data sheet

Power tools for trade & industry

ANGLE EXACT NFC 15-500

INDUSTRIAL ANGLE EXACT NFC 15-500



The new EXACT screwdrivers – now with lithium-ion technology!

The most important data

Torque (hard)	2 – 15 Nm
Speed	50 – 520 rpm

Part Number 0 602 494 B01

Technical data

Technical data

Description	Angle Wrench
Torque, from (hard)	2 Nm
Torque, to (hard)	15 Nm
Torque (hard)	2 – 15 Nm
Torque, from (soft)	2 Nm
Torque, to (soft)	15 Nm
Torque (soft)	2 – 15 Nm
Speed, from	50 rpm
Speed, up to	520 rpm
Speed	50 – 520 rpm
Direction of rotation	R/L
Weight	107 kg
Comment	Below 50% speed setting eventually lower power
Bit holder	Without angle head
Battery	18 V / 2.0 Ah battery
Drive type	Battery
Design	Angle
Adjustable speed	+
Brushless motor	+
Other torque range possible	+
Lever/trigger start	+

Connector type	Shut-off clutch
----------------	-----------------

Noise/vibration information

Screwdriving

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

