Features

- ChA, ChB Counting, Reset, Pause Input
- Configurable Counter, Totalizer Batch Counter,Timer, Chronometer, Frequencymeter and Tachometer
- 6 Digits (PV) Display
- 100...240Vac Power Supply
- ModBus RS-485 RTU Serial Communication
- 96X48mm Panel Dimension

RS PRO Timer & Counter

RS Stock No:
874209



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Timer & Counter
2X Input (ChA, ChB)
2X Relay Output (3A@250Vac)
Reset and Pause Input
ModBus RS-485 RTU Communication
Configurable ;
- Counter,
- Totalizer Batch Counter,
- Timer,
- Chronometer,
- Frequencymeter,
- Tachometer

General Specifications

Supply Voltage and Power	100...240Vac 50/60Hz – 2,5A
Sensor Inputs	Reset, Pause and ChA-ChB Counting Inputs
Relay Outputs	2X Relay Output (3A@250Vac)
Communication	ModBus RS-485 RTU

Mechanical Specifications

Dimension	96 mm x 48 mm 86,5 mm
Panel	IP65 at front, IP20 at rear
Max. Operating Temperature / Humidity	50°C / 90 % max. (None condensing)

Electrical Connection

