



Product number 1175470010
EAN 4007123674534

TECHNICAL DATA

Luminous flux	570 lm
Power consumption	7.1 W
Luminous efficacy	90.3 lm/W
Energy efficiency class	
Colour temperature	6500 K

Min.-Max. Nominal input voltage	220 V - 250 V
Lifetime	54000 h
Impact strength	IK07
Protection class	II
Degree of protection (IP)	IP65
Colour	black/yellow

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	0.61 kg
Dimension LxWxH (without packing)	4 cm x 12 cm x 34 cm

Weight of product (including packaging)	0.74 kg
Dimension LxWxH (incl. packing)	7 cm x 8.7 cm x 37.5 cm