

Datasheet

RS Pro 5000mm PVC Aluminium Foil HVAC Ducting, 150mm diameter

RS Stock No: **679-8719**



Product Details

RS Pro HVAC ducting measures 150 x 5000 mm and has PVC aluminium foil construction. It has a covered, metal, corrosion-resistant spiral helix, which allows the ducting to be compressed and provides good crush and kink resistance during handling and installation. This ducting is suitable for operating temperatures ranging from -5 to +90°C.

Features and Benefits

- Both types have a covered, metal, corrosion-resistant spiral helix, which allows the ducting to be compressed
- Offers good crush and kink resistance during handling and installation
- Fire retardant to meet the requirements of BS476: parts 6, 7 and 20
- Operating temperature of -5 to +90°C



Specifications:

Diameter	150 mm
Length	5000 mm
Material Type	PVC Reinforced Aluminium Foil
Maximum Operating Temperature	+90°C
Minimum Operating Temperature	-5°C
Operating Temperature Range	-5 to +90°C