

DWS774-QS

Radial miter saw 1400W 216 mm



5035048614099



Product Description:

Power: 1400W Ø of blade / bore (mm): 216 / 30 No load speed (rpm): 3750 Head tilt (°): 48 Miter cuts L/R (°): 48 / 48 90° cutting cap (h x W mm): 62 x 250 45° cutting cap (h x W mm): 48 x 190

Product features and benefits:

- Sliding and graduated stop located on the left and right for better holding and material guidance Side handles for easy transport Pre-set
- saw head rotation angles at 15°, 22.5°, 30°, 45°, 90° and quick
- positioning up to 50° Compact rail guide designed to offer high cutting capacity in an easily transportable format New 1400 watt motor for high cutting capacities
-
- Regardless of the material The sliding lock of the saw head allows classic cuts to be made and the machine to be transported safely
-
- Improved dust filter The table and rear fence have been machined to provide the precision required by most applications The classic design has been improved and updated for the modern user The XPS indicator always shows the cut line with extreme accuracy
-

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Mounting bolts (x2)
- Clamping jaw (x1)
- Carbide Blade (x1)
- Service Key (x1)

Specifications techniques :

- Power supply: 1400 W
- - Maximum cutting depth: 70 x 20 mm
 - Blade bore: 30 mm
 - Blade diameter: 216 mm
 - Capacity (90°/45°): 250 x 60 mm
 - Capacity
 - Maximum cut (45°/90°): 170 x 60 mm Saw blade thickness: 2.6 mm Capacity
 -
 - cutting Maximum (90°/45°): 250 x
 - 48 mm Blade speed: 4600 rpm Maximum cutting capacity (45°/45°): 170 x
 -
 -

48 mm

