
























Vista anteriore inserto maschio  
 Front view of male insert

<b>2 CONTATTI</b> <b>2 CONTACTS</b>  ARRANGEMENT CONTACT SIZE SERVICE RATING	  	<b>3 CONTATTI</b> <b>3 CONTACTS</b>     
	8-2 20 I  10-2 16 II  16-2 16 I	8-3 20 I  8-3A 20 I  8-33 20 I  12-3 16 II
<b>4 CONTATTI</b> <b>4 CONTACTS</b>  ARRANGEMENT CONTACT SIZE SERVICE RATING	 	<b>5 CONTATTI</b> <b>5 CONTACTS</b>  
	8-4 20 I  12-4 16 I	14-5 16 II
<b>6 CONTATTI</b> <b>6 CONTACTS</b>  ARRANGEMENT CONTACT SIZE SERVICE RATING	 	<b>7 CONTATTI</b> <b>7 CONTACTS</b>  
	10-6 20 I  10-98* 20 I	10-7 20 I
<b>8 CONTATTI</b> <b>8 CONTACTS</b>  ARRANGEMENT CONTACT SIZE SERVICE RATING	  	<b>10 CONTATTI</b> <b>10 CONTACTS</b>  
	10-8 20 I  12-8 20 I  16-8 16 II	12-10 20 I
<b>11 CONTATTI</b> <b>11 CONTACTS</b>  ARRANGEMENT CONTACT SIZE SERVICE RATING		<b>12 CONTATTI</b> <b>12 CONTACTS</b>   
	18-11 16 II	14-12/3 16 II  14-12 8-20,4-16 I
<b>14 CONTATTI</b> <b>14 CONTACTS</b>  ARRANGEMENT CONTACT SIZE SERVICE RATING	 	<b>15 CONTATTI</b> <b>15 CONTACTS</b>  
	12-14 20 I  14-14* 20 I	14-15 14-20,1-16 I


 LEGENDA CONTATTI  
 CONTACT LEGEND

 \*CONSULTARE L'AZIENDA  
 \*CONSULT FACTORY

# Disposizione contatti Contact arrangements




## 16 CONTATTI 16 CONTACTS



ARRANGEMENT  
CONTACT SIZE  
SERVICE RATING

20-16\*  
16  
II

## 18 CONTATTI 18 CONTACTS



14-18\*  
20  
I


## 19 CONTATTI 19 CONTACTS



ARRANGEMENT  
CONTACT SIZE  
SERVICE RATING

14-19  
20  
I

## 21 CONTATTI 21 CONTACTS




22-21\*  
16  
II

## 23 CONTATTI 23 CONTACTS



ARRANGEMENT  
CONTACT SIZE  
SERVICE RATING

16-23  
22-20,1-16  
I



16-99  
21-20,2-16  
I

## 24 CONTATTI 24 CONTACTS



20-24\*  
20  
I

## 25 CONTATTI 25 CONTACTS



ARRANGEMENT  
CONTACT SIZE  
SERVICE RATING

20-25\*  
20  
I

## 26 CONTATTI 26 CONTACTS



16-26  
20  
I

## 27 CONTATTI 27 CONTACTS



ARRANGEMENT  
CONTACT SIZE  
SERVICE RATING

20-27\*  
20  
I

## 30 CONTATTI 30 CONTACTS




18-30\*  
29-20,1-16  
I

## 32 CONTATTI 32 CONTACTS




ARRANGEMENT  
CONTACT SIZE  
SERVICE RATING

18-32  
20  
I



22-32\*  
20  
I

## 34 CONTATTI 34 CONTACTS




22-34\*  
20  
I

LEGENDA CONTATTI  
CONTACT LEGEND



\*CONSULTARE L'AZIENDA  
\*CONSULT FACTORY

**36 CONTATTI**  
**36 CONTACTS**


 ARRANGEMENT  
 CONTACT SIZE  
 SERVICE RATING

 22-36\*  
 20  
 I

**39 CONTATTI**  
**39 CONTACTS**


 20-39\*  
 37-20,2-16  
 I


**41 CONTATTI**  
**41 CONTACTS**

 ARRANGEMENT  
 CONTACT SIZE  
 SERVICE RATING

 20-41\*  
 20  
 I

 22-41  
 27-20,14-16  
 I


**55 CONTATTI**  
**55 CONTACTS**


 ARRANGEMENT  
 CONTACT SIZE  
 SERVICE RATING

 22-55  
 55  
 I


**61 CONTATTI**  
**61 CONTACTS**

 24-61\*  
 20  
 I

**Rotazioni degli inserti / Insert rotation**

 Posizione normale  
 con contatti maschio

 Normal position  
 with pin contacts

 Posizione ruotata  
 con contatti femmina

 Alternate position  
 with socket contacts

 Posizione ruotata  
 con contatti maschio

 Alternate position  
 with pin contacts

 LEGENDA CONTATTI  
 CONTACT LEGEND

 \*CONSULTARE L'AZIENDA  
 \*CONSULT FACTORY