

Housing units UCT204 (Series UCT)

cast iron housing, radial insert ball bearing with grub screws in inner ring, RSR seals, for linear motion

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	20 mm
L	94 mm
H	89 mm
A	32 mm
A1	12 mm Tolerance: +0,2/0
A2	21 mm
B	31 mm
H1	76 mm Tolerance: 0/-0,5
L1	61 mm
L2	10 mm
L3	51 mm
N	19 mm

N ₁	16 mm	
N ₂	32 mm	
S ₁	18,3 mm	
T	51 mm	
m	0,72 kg	Mass
	T204	Designation, housing
	UC204	Designation, radial insert ball bearing



