

Rittal – The System.

Faster – better – everywhere.

► System windows for VX, TS, SE – FT 2735.500

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



System windows for VX, TS, SE – FT 2735.500

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Design: 30 section

Description: To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access.

Benefits:

- Base frame: Easily screw-fastened to the door thanks to modified dimensions (tubular door frame may be used as a drilling template).
- Base frame: Readily height-adjustable.
- Base frame: Stabilises the door cut-out.
- Base frame: Conceals the cut edge.
- Base frame: There is no dirt on the seal, the glass is protected from being lifted out, dirt cannot drop inside, and moisture cannot run behind the window when opening.
- Base frame: Frame section height 30 mm or 60 mm
- Viewing window: Made from single-pane safety glass: High level of resistance to solvents and scratches, anti-static, reduced risk of injury if broken.
- Viewing window: Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).
- Viewing window: Hinge with 180° opening angle, easily inserted.

Material: Extruded aluminium section with die-cast zinc corner pieces and single-pane safety glass.

Surface finish: Base frame: Powder-coated on the outside in RAL 7035
Hinge and lock section: Natural-anodised

Protection category IP to IEC 60 529: IP 54

Note: Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).
Not suitable for outdoor siting

Product description

To fit:	Enclosure type: VX Enclosure type: TS Enclosure type: SE Width: = 600 mm
Dimensions:	Width: 500 mm Height: 270 mm Depth: 47 mm
Viewing area:	Width: 363 mm Height: 198 mm
Build depth for components (max.):	33 mm
Packs of:	1 pc(s).
Weight/pack:	3.3 kg
Copper weight (kg per piece):	0
EAN:	4028177476288
Customs tariff number:	76101000
ETIM 7.0:	EC002527
ETIM 6.0:	EC002527
eCl@ss 8.0/8.1:	27182301
eCl@ss 6.0/6.1:	27182301
Product description:	FT System window, for TS, SE, 30 section, WHD: 500x270x47 mm, for W: 600 mm
Approvals	
Certificates:	NA Protection category