

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability
- **Flanged Design:** Ensures secure positioning and easy installation
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads
- **Bore Size of 1.37 in:** Compatible with a wide range of shafts
- **Outside Diameter of 1.62 in:** Fits standard housing dimensions
- **Width of 3/4 in:** Compact design for space-constrained applications

RS PRO 1.37 in Flanged Plain Bearing

RS Stock No: 518-174



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

The RS PRO Flanged Plain Bearing is designed for applications requiring reliable rotational or linear motion. Made from sintered bronze, this bearing offers excellent wear resistance and durability, making it ideal for various industrial environments. Its flanged design ensures secure positioning and easy installation.

General Specifications

Bore Size	1.37 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	1.62 in
Width	3/4 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

