

Hot Air Irons and Nozzles

Hot Air Nozzles for 700 W Hot Air Stations

Four sides heated (Type NQ)



		Order No.	Model	Description	Length X	Width Y
		005 87 368 39	NQ05	Hot air nozzle, four sides heated	10,7 mm	10,7 mm
		005 87 368 38	NQ15	Hot air nozzle, four sides heated	14,5 mm	10,0 mm
		005 87 368 18	NQ10	Hot air nozzle, four sides heated	14,8 mm	14,8 mm
		005 87 368 37	NQ20	Hot air nozzle, four sides heated	15,5 mm	13,0 mm
		005 87 368 14	NQ25	Hot air nozzle, four sides heated	18,0 mm	18,0 mm
		005 87 507 21	NQ30	Hot air nozzle, four sides heated	17,5 mm	23,5 mm
		005 87 368 07	NQ35	Hot air nozzle, four sides heated	20,5 mm	20,5 mm
		005 87 368 80	NQ	Hot air nozzle, four sides heated	24,0 mm	12,0 mm
		005 87 368 04	NQ40	Hot air nozzle, four sides heated	26,0 mm	26,0 mm
		005 87 368 33	NQ45	Hot air nozzle, four sides heated	31,3 mm	31,3 mm
		005 87 368 91	NQ50	Hot air nozzle, four sides heated	36,0 mm	36,0 mm
		005 87 368 90	NQ55	Hot air nozzle, four sides heated	43,0 mm	43,0 mm