

FR12 - Modaflame Knit FR Sweatshirt

Collection: Modaflame™ Knit

Range: Flame Resistant Multi-Norm

Shell Fabric: Modaflame Knit: 60% Modacrylic, 39% Cotton, 1% Carbon Fibre, 300g

Outer Carton: 24

Product information

Ideal for workers exposed to heat in their working environment. Features on this garment include raglan sleeve, round neck, ribbed collar and cuffs, making it comfortable and easy to wear.

Modaflame™ Knit

Constructed from an inherently fire resistant yarn of 60% Modacrylic, 39% Cotton and 1% Carbon Fibre. Modaflame™ Knit is strong, durable, and highly innovative. The high performance fibres are blended without any chemical treatment giving Modaflame™ Knit it's unparalleled soft, natural touch and appearance.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1, B1, C1, F1)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 9.2 CAL/CM², ATPV 15 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

ASTM F1959/F1959M-12 (ATPV=16 Cal/CM² (HAF=86%))



Features

- Inherent flame resistant qualities will not diminish with washing
- Protection against radiant, convective and contact heat
- High cotton content for superior comfort
- Ribbed cuffs for added comfort
- Ribbed hem for a comfortable fit
- External standards label for quick identification of protection levels
- Outstanding colour fastness and shrinkage results
- Crew neck
- Anti-static
- 40+ UPF rated fabric to block 98% of UV rays
- CE-CAT III

FR12 - Modaflame Knit FR Sweatshirt

Commodity Code: 6110309100

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/12776-05/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR12BKRXS	Black	55.0	36.0	32.0	0.9990	0.0634	5036108508952	15036108993809
FR12BKRS	Black	55.0	36.0	32.0	0.9990	0.0634	5036108245567	15036108734068
FR12BKRM	Black	55.0	36.0	32.0	0.9990	0.0634	5036108245550	15036108734051
FR12BKRL	Black	55.0	36.0	35.0	0.9990	0.0693	5036108245543	15036108734044
FR12BKRXL	Black	55.0	36.0	35.0	0.9990	0.0693	5036108245574	15036108734075
FR12BKRXXL	Black	55.0	36.0	35.0	0.9990	0.0693	5036108245581	15036108734082
FR12BKRXXXL	Black	55.0	36.0	35.0	0.9990	0.0693	5036108245598	15036108734099
FR12BKR4XL	Black	55.0	36.0	35.0	0.9990	0.0693	5036108508945	15036108993793