

Datasheet

RS PRO ispot Driverless Square LED Bulkhead

Description

The ispot driverless bulkhead is the most advanced LED bulkhead on the market. It boasts an attractive ultra-thin design with a depth of only 36mm. The ispot driverless bulkhead is tamper proof with no visible screws on the front and tamper proof screws are hidden on the back.

Available in Daylight with a Black or White finish.

Range

RS PRO ispot 10W 5700K Black

RS Stock No

111-6502



Dimensions (mm), Beam Angle & Lumens

RS Stock No.	Lumen Output	Beam Angle	Fitting Dimensions (Diameter x Depth)
111-6502	550lm	110°	180Ø x 36mm

Features

- Innovative high voltage LED chips – no driver required
- Daylight (5700K)
- High grade aluminium body and polycarbonate diffuser
- Impact resistant
- Available in Black and White finishes
- 36000 hours rated life
- IP54

Technical Specification

Voltage	220-240VAC~ 50/60Hz
Lamp	SMD LED
Colour temp.	5700K (Daylight)
IP rating	IP54

Standards

- BS EN 60598-1+A11
- BS EN 60598-2-1
- BS EN 60598-2-5
- BS EN 62471
- BS EN 62493
- BS EN 55015+A2
- BS EN 61547
- BS EN 61000-3-2+A2
- BS EN 61000-3-3