

2154SK 14

3C-Screwdriver with striking cap

for slotted head screws

Code	ETIM
1845284	EC000158
EAN	UNSPSC
4010886857250	27-11-17-01
Country of origin	eCl@ss
Slovenia	21-04-04-01
Customs tariff number	
82054000	



Article description

- Acc. to DIN ISO 2380-2, cutting edge according to DIN ISO 2380-1 Form A
- 3-component Power-Grip³ handle with impact cap
- Ergonomic handle shape for accurate, non-tiring work
- Positive-fit joint of handle and blade for optimum transmission of force
- Hexagon blade with additional hexagon bolster
- Blade of galvanised molybdenum-vanadium steel

Article information

Contents (Qty of pieces)	1	Cap rotatable	no
Net weight [kg]	0,324 kg	Anti-magnetic	no
Total length [mm]	370 mm	Ball head	no
Total width [mm]	37 mm	Handle available	yes
Total height [mm]	32 mm	Isolated	no
Material	Molybdenum-vanadium-steel	Corrosion Protected	no
Drive connector hexagon male (metric)	16,0 mm	Colour coding	no
Blade length	250 mm	Unit-tested	no
Standard	DIN ISO 2380-2	Handle design	3C
Blade width [mm]	14,0 mm	Output tip reference standard	DIN ISO 2380-1 - Form A
Low sparking design	no	Drive hexagon	yes
Blade shape	Hexagon	Blade thickness	2,5 mm
Roll protection	no	Blade thickness	2,5 mm
Impact cap	yes		