

DCMHT562N-XJ

Hedge trimmer XR 18V 19 mm

5035048838600



Product Description:

Variable Speed (cps/min): 0-2800 Gap (mm): 19 Blade Length (cm): 55



Product features and benefits:

- FAST CUTS: 55 cm cutter bar with 19 mm spacing to quickly and easily trim hedges UNINTERRUPTED PERFORMANCE: up to 75 minutes of autonomy, *so you can trim your hedges with less need for recharging.* (with a DEWALT DCB184 battery. Battery

sold separately.)

- COMFORTABLE: with only 3.2 kg, ergonomic overmolded handles, it allows you to maneuver easily and reduce fatigue.
- SLIM PROFILE DESIGN: 39% narrower body design compared to the previous generation.
- OPTIMAL CONTROL: The D-handle design makes it easy to activate the machine regardless of the operator's position. EASY TO STORE:
- The wall mounting hook on the underside of the hedge trimmer allows you to store it easily. CLEAR DEBRIS: Compatible with the DEWALT
- Deflector to easily push debris out of the hedge during trimming.

(Accessory sold separately) XR18V SYSTEM: The power of

- wired, the freedom of wireless.

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Hedge trimmer XR 18V (x1)

DCMHT562N-XJ

Hedge trimmer XR 18V 19 mm



5035048838600

Part of the DCMHT562N series

Ref	▲ ▼ Title	▲ ▼
DCMHT562N-XJ	Hedge trimmer XR 18V 19 mm	