









# CONTRE-ÉCROU plastique



Couleur : RAL 7035  
 Matière : PA6 FV  
 Norme : EN 50262  
 EN 60423  
 Guide UTE 68311

 métrique	 mm	 mm	Longueur de filetage	Code	
M 12		19	5	G 4312 010	100
M 16		22	5	G 4316 010	100
M 20		24	5	G 4320 010	50
M 25		30	6	G 4325 010	25
M 32		38	7,5	G 4332 010	20
M 40		50	8	G 4340 010	10
M 50		60	9	G 4350 010	10
M 63		75	10	G 4363 010	10

 PG	 mm	 mm	Longueur de filetage	Code	
PG 07		15	5	G 4107 010	100
PG 09		19	5	G 4109 010	100
PG 11		22	5	G 4111 010	50
PG 13		24	5	G 4113 010	50
PG 16		27	6	G 4116 010	50
PG 21		32	6,5	G 4121 010	25
PG 29		41	7,5	G 4129 010	15
PG 36		59	8	G 4136 110	10
PG 42		64	9	G 4142 010	10
PG 48 NFC		70	9,5	G 4148 010	10
PG 48 DIN		70	9,5	G 4149 010	10