



RE936-07

- Multiadapter SOP28, SOIC28, SOIC28w, HSOP28, SO28
- Epoxy fibre-glass 1.50 mm
- Double-sided 35 µm Cu
- Plated through holes (PTH)
- Surface chem. Ni/Au
- Solder stop mask
- Adaption circuit board for SOP28, SOIC28, SOIC28w, HSOP28, SO28
- Pitch 1.27 mm
- Hole spacing 2.54 mm
- Two experimenting areas with 2 x 4 square pads 2.20 x 2.20 mm
- Shield pad & cooling pad
- Size 36.83 x 26.67 mm