

# Product information

## Circular Saw 210mm



Satisfying the professional's needs

### 5008MGJ

Depth of Cut @ 90°	75.5 mm
Blade Diameter	210 mm
Depth of Cut @ 45°	57 mm
Max Cut @ 50°	51.5 mm
Bore Diameter	30 mm
Input Wattage	1800 w
No Load Speed	5200 rpm
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration: Cutting Wood	3 m/sec <sup>2</sup>
Net weight	4.8 kg
Supplied with MAKPAC Case	1



- Easy to read Cut-depth scale with the two numbers most frequently used, 19mm (3/4") and 13mm (1/2"), stamped in larger size.
- Maximum Cutting Depth of 75.5mm (3")
- Built-in Job Light Using Twin LED Light
- Lightweight, only 4.8kg Tool weight has been reduced by using magnesium die cast for base, blade case and safety cover.
- Max Bevel Capacity: 50 degrees

Details correct as of: 29-7-2015

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)