

FEATURES

- Liquid Tight
- High mechanical strength
- -50°C to +135°C

RS PRO Liquid Tight Nickel Plated Brass Male Flexible Conduit Elbow Gland 32mm

RS Stock No.: 2149577



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to

Flexible Conduit Gland

the leading brands without paying a premium price.

General Specifications

Material	Nickel Plated Brass
Colour	Self Colour
Conduit Type	Flexible
Qty per pack	2
Maximum Operating Temperature	+135°C
Minimum Operating Temperature	-50°C
Nominal Size	32mm
Thread Size	M32

Compatible Conduits

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
2149568	RS PRO	Flexible Conduit	Galvanised Steel PVC Cover	IP66, IP67	-20°C to +105°C