



Humfree Contactor 25A, 2NO, 24V

ESD225S

Technical Properties

Type of contacts	2NO
Override	No
Rated current	25 A
Rated operational voltage Ue	230 V
Frequency	50/60 Hz
type of connection	with screw
Connection cross-sect. rigid cable	1 / 10mm <sup>2</sup>
Connection cross-sect. flexible cable	1 / 6mm <sup>2</sup>
Command voltage AC	24 V
Rigid cable connect. cross-sect. for control	1 to 10 mm <sup>2</sup>
Max cable connect. cross section (flexible) for control	1 to 6 mm <sup>2</sup>
Inrush power absorbed	2,2 VA
Operating consumption	2,2 VA
Number of mechanical operations	100000
Electric endurance in number of cycles	30000
Operating temperature	-10 to 50 °C
Storage temperature	-40 to 80 °C
Protection index IP	2
Number of modules	1