Prism Pro XM

Part of the Downlights product category

Model	Prism Pro XM Gimbal Fire Rated Downlight
Code	APRIPGXM/1
Application	Residential

GENERAL INFORMATION

Input	220-240V
Wattage	5W/7W
Operating Temp	-10°C - 35°C
Lumens Delivered	580lm - 745lm (4000K)
lm/W	120lm/W
CCT	2700K/3000K/4000K/6000K
UGR	28
Beam Angle	55

MATERIAL INFORMATION

Main Material	Polycarbonate, Steel
Product Weight without Packaging	0.29 kg
Colour / Finish	White
Diameter	88 mm
Height	73 mm

TECHNICAL INFORMATION

Class Protection	2
Light Source	LED
SDCM (Initial Macadam)	5
CRI	80
Internal / External	Internal
Surface / Recessed / Suspended	Recessed
Power Factor	0.95
L70 @ 25°C	L70 60,000h

PRODUCT FEATURES

- 220-240V IP65 dimmable LED 4 CCT selectable fire rated performance gimbal suitable for residential and hospitality applications
- TM66 2.5 assessed – independently evaluated against the industry standard for measuring the circularity of lighting products.
- CCT selectable between 2700K, 3000K, 4000K and 6000K and power selectable; offering a choice of 2 outputs, in one luminaire
- 30° tilt angle
- Innovative 2 part detachable connector design allows initial wiring and testing to be completed first, then simply plug the downlight back to the connector, ensuring a quick and simple installation

ACCESSORIES

APRIPXM/AG/LE/1	Prism Pro XM Anti-glare Replacement Light Engine
APRIPXM/DRI/1	Prism Pro XM Universal Replacement Driver
APRIPGXMBZ/BK	Prism Pro XM Gimbal Bezel - Matt Black
APRIPGXMBZ/SC	Prism Pro XM Gimbal Bezel - Satin Chrome
APRIPGXMBZ/CH	Prism Pro XM Gimbal Bezel - Chrome
APRIPGXMBZ/AB	Prism Pro XM Gimbal Bezel - Antique Brass
APRIPXM/CP/BK	Prism Pro XM Converter Kit - Matt Black
APRIPXM/CP/SC	Prism Pro XM Converter Kit - Satin Chrome
APRIPXM/CP/CH	Prism Pro XM Converter Kit - Chrome
APRIPXM/CP/AB	Prism Pro XM Converter Kit - Antique Brass





Prism Pro XM

Part of the Downlights product category

Model	Prism Pro XM Gimbal Fire Rated Downlight
Code	APRIPGXM/1
Application	Residential





