



Main

[Us] rated supply voltage	3.6 V nominal
Battery type	Lithium integrated
Battery life	10 yr 2 frames/day 4 yr 10 frames/day 2 yr 20 frames/day
Number of inputs	2 dry contact input(s)
Electrical connection	Cable
Product or component type	Wireless transmitter
Operating system	Mac iOS Android
Web services	Links to Schneider Electric web site Smartphone app
Mode of transmission	1 status frame per day On change on one of the inputs
Acquisition speed	6 frames/h 50 frames/day
Fixing mode	By screws
Radio frequency fields	868 MHz

Complementary

Product destination	Pressure switch XMLA Pressure switch XMLB Pressure switch XMLC Pressure switch XMLD Limit switch XCM Limit switch XCKM Limit switch XCKL Limit switch XCKS Limit switch XCKJ Limit switch XCKN Limit switch XCKP Limit switch XCKT Limit switch XCKD
Type of license	Registration on radio network included (5 years)
Communication network type	Sigfox Europe
Transmission rate	100 bit/s
Height	100 mm

Length	45 mm
Width	50 mm
Product weight	0.216 kg
Radio power	14 dBm
Operating distance	<= 10000 m

Environment

Directives	1999/5/EC - R&TTE directive
Product certifications	SIGFOX ready CE
Standards	ETSI EN 300 220-2 EN 62368-1
Ambient air temperature for operation	-25...70 °C
IP degree of protection	IP66