

Other accessories



SET OF 2 INSULATION-PIERCING CLIPS (R/B) 30 V_{AC}, 60 V_{DC}
> P01102055Z



Current lead equipped with a French 2P+E power socket
For inserting an ammeter in series and in total safety to measure current with a current clamp without removing the external sheath of the power supply cable
> P03295509



Measurement lead for French and German 2P+E power sockets
For direct measurement on a mains socket
Quick implementation and reliable connections
> P06239307



Set of 2 adapters
Male BNC - insulated female sockets (R/B) Ø 4 mm with 19 mm spacing - 500 V CAT I, 150 V CAT III
> P01101846



External charger module + 4 x AA Ni-MH batteries
> HX0053



Set of 2 adapters
Male BNC - Insulated male sockets (R/B) Ø 4 mm with 19 mm spacing
500 V CAT I, 150 V CAT III
> P01101847



CMS clamp
Copper-Gold-plated Beryllium contacts - Output via male plugs Ø 4 mm - Length 1.20 m - SELV
> HX0064



SHT40KV
High-voltage probe for multimeters
Max. rated voltage: 40kVDC, 28 kVrms or 40 kVpeak
Division ratio (input/output): 1 kV/1 V
> P01102097



C.A 753
Measurement adapter for European 2P+E and Schuko sockets
- Suitable for measurements on P (Phase), N•(Neutral) and PE (Earth) conductors in total safety
- Guarantees mechanical and electrical contact with all test probes (Ø2, Ø4, IP2X, etc.)
- Shows the presence of a P-N voltage (> 200 V) and indicates the position of the phase

Temperature measurement

Adapters



Set of 2 thermocouple safety adapters for multimeters
Female thermocouple plug - Insulated male plugs (R/B) Ø 4 mm with 19 mm spacing
> P01102106Z



Pt100/Pt1,000 probe adapter for multimeters
Female Pt100/Pt1,000 plug - Insulated male plugs (R/B) Ø 4 mm
> HX0091



Safety adapter and K-sensor temperature probe
- For multimeters and clamp multimeters equipped with a temperature measurement calibre with banana inputs with 19 mm spacing
- Measurement range from -50 °C to +350 °C
> P01102107Z