



Technical data model HTP and model HTG

| Model | EAN-No. 4025092* | Capacity kg | Size | Beam flange width b mm | Beam flange thickness t max. mm | Curve radius min. m | Hand effort at WLL daN | Weight* kg | Weight* with locking device kg |
|--------------------|---------------------|----------------|------|---------------------------------|--|---------------------------|------------------------------|---------------|---|
| HTP 500 (7938713) | *054874 | 500 | A | 50 - 220 | 25 | 0.9 | - | 8.0 | 14.5 |
| HTP 1000 | *054881 | 1000 | A | 50 - 220 | 25 | 0.9 | - | 9.0 | 17.0 |
| HTP 2000 (7938722) | *054898 | 2000 | A | 66 - 220 | 25 | 1.15 | - | 16.0 | 24.0 |
| HTP 3000 | *054904 | 3000 | A | 74 - 220 | 25 | 1.4 | - | 32.0 | 41.2 |
| HTP 5000 | *054911 | 5000 | A | 90 - 220 | 25 | 1.8 | - | 48.0 | 58.5 |
| HTP 500 | *054928 | 500 | B | 160 - 300 | 40 | 0.9 | - | 10.6 | 17.1 |
| HTP 1000 | *054935 | 1000 | B | 160 - 300 | 40 | 0.9 | - | 12.0 | 20.0 |
| HTP 2000 | *054942 | 2000 | B | 160 - 300 | 40 | 1.15 | - | 19.3 | 27.3 |
| HTP 3000 | *054959 | 3000 | B | 160 - 300 | 40 | 1.4 | - | 35.8 | 45.0 |
| HTP 5000 | *054966 | 5000 | B | 180 - 300 | 40 | 1.8 | - | 52.2 | 62.7 |
| | | | | | | | | | |
| HTG 500 | *074711 | 500 | A | 50 - 220 | 25 | 0.9 | 3 | 9.7 | 16.2 |
| HTG 1000 | *074728 | 1000 | A | 50 - 220 | 25 | 0.9 | 6 | 11.2 | 19.2 |
| HTG 2000 | *074735 | 2000 | A | 66 - 220 | 25 | 1.15 | 7 | 18.0 | 26.0 |
| HTG 3000 | *074742 | 3000 | A | 74 - 220 | 25 | 1.4 | 7 | 35.4 | 44.6 |
| HTG 5000 | *074759 | 5000 | A | 90 - 220 | 25 | 1.8 | 9 | 51.8 | 62.3 |
| HTG 500 | *074766 | 500 | B | 160 - 300 | 40 | 0.9 | 3 | 12.6 | 19.1 |
| HTG 1000 | *074841 | 1000 | B | 160 - 300 | 40 | 0.9 | 6 | 14.1 | 22.1 |
| HTG 2000 | *074773 | 2000 | B | 160 - 300 | 40 | 1.15 | 7 | 21.3 | 29.3 |
| HTG 3000 | *074780 | 3000 | B | 160 - 300 | 40 | 1.4 | 7 | 39.2 | 48.4 |
| HTG 5000 | *074797 | 5000 | B | 180 - 300 | 40 | 1.8 | 9 | 56.0 | 66.5 |
| HTG 8000 | *074803 | 8000 | B | 125 - 310 | 40 | 1.8 | 14 | 104.0 | - |
| HTG 10000 | *074810 | 10000 | B | 125 - 310 | 40 | 1.8 | 14 | 104.0 | - |
| HTG 15000 | *074827 | 15000 | B | 125 - 310 | 40 | 5.0 | 29 | 230.0 | - |
| HTG 20000 | *074834 | 20000 | B | 125 - 310 | 40 | 5.0 | 29 | 230.0 | - |

*Weight HTG: without hand chain



Available in explosion proof version.