## 9001SKR24GH5

Pushbutton , Non-Illuminated, Momentary, Type: SK, Size: 30mm, 10A, 600V

## **Technical Characteristics**

Bezel Material	Plastic
Button/Cap Color	Green
Ampere Rating	10A
Approvals	UL Listed File Number E42259 CCN NKCR - CSA Certified File Number LR25490 Class 3211 03 - CE Marked
Button Type	Screw-In Mushroom with Set Screw (1.38 Inch)
Guard Type	Full Guard
Catalog Reference Number	9001CT0001
Contact Configuration	1 N.O.
Contact Material	Silver Alloy
Enclosure Type	Water tight, Dust tight, Oil tight and Corrosion Resistant (Indoor/Outdoor)
Enclosure Rating	NEMA 4/4X/13
Head Type	Round
Maximum Voltage Rating	600V
Mounting Type	Panel
Mounting Position	All
Number of Operators	1
Operator Action	Momentary
Operator Type	Non-Illuminated
Terminal Type	Screw Clamp
Туре	SK
Size	30mm
Utilization Category	AC15 - DC13

## **Shipping and Ordering**

Category	21429 - Push Buttons, Corrosion Resistant, Type SK & SKY
Discount Schedule	CP1
Article Number	785901042181
Package Quantity	1
Weight	0.5 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

