


Push-in L-fitting NPQO-L-G38-Q10-P5

Part number: 8203310

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	8 mm
Tubing insertion depth	20.1 mm
Type of seal on screwed plug	O-ring
Mounting position	Any
Design	L-shape
Size of pack	5
Design	Push-pull principle
Variants	With mounting holes
Operating pressure complete temperature range	-0.09 MPa ... 0.3 MPa
Operating pressure complete temperature range	-0.9 bar ... 3 bar
Operating pressure complete temperature range	-13.05 psi ... 43.5 psi
Temperature-dependent operating pressure	-0.09 MPa ... 1.2 MPa
Temperature-dependent operating pressure	-0.9 bar ... 12 bar
Temperature-dependent operating pressure	-13.05 psi ... 174 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gas Carbon dioxide Air Oxygen Nitrogen
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Media temperature	0 °C ... 120 °C
Ambient temperature	0 °C ... 60 °C
Biocompatibility according to standard	ISO 18562
Oxygen suitability according to standard	ASTM G 93 ISO 15001
Maximum impurity level for hydrocarbons	550 mg/m ²
Max. tightening torque	10 Nm
Nominal torque	9 Nm
Tolerance for nominal tightening torque	±10%
Product weight	41.79 g
Pneumatic connection, port 1	Male thread G3/8
Pneumatic connection, port 2	For tubing outside diameter of 10 mm
Ambient temperature	32 °F ... 140 °F
Colour of release ring	White

Feature	Value
Material screwed plug	High-alloy stainless steel
Note on materials	RoHS compliant
Material housing	PVDF
Material thread seal	Fluoro rubber
Material release ring	PVDF
Material o-ring	Fluoro rubber
Material tubing seal	Fluoro rubber
Material tubing clamp component	High-alloy stainless steel
Thrust ring material	PVDF