

## FEATURES

- **LED Light Source:** Provides energy-efficient and long-lasting illumination.
- **Steady Light Effect:** Ensures consistent visibility for effective signalling.
- **Sound Level of 88-92 dB:** Delivers a clear audible alert suitable for noisy environments.
- **24 V DC Operation:** Compatible with standard DC power supplies.
- **Grey ABS Housing:** Offers durability and resistance to impact.
- **IP43 Rating:** Protects against solid objects over 1mm and water spray.
- **Screw Mount Type:** Facilitates easy and secure installation.

## RS PRO LED Horn-Beacon Combination, Grey ABS Housing

RS Stock No: 658-303



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO Horn-Beacon Combination is a versatile signalling device designed for industrial environments. It combines both visual and auditory alerts, making it ideal for situations where clear communication is critical. This device is perfect for enhancing safety and ensuring compliance with industry standards.

## General Specifications

Bulb Type	LED
Housing Colour	Grey
Lens Colour	Red
Light Effect	Steady
Mount Type	Screw
Number of Tones	1
Product Type	Horn-Beacon Combination
Sounder Type	Sounder Beacon

## Electrical Specifications

Current Consumption	0.32 A
Current Type	DC
Maximum Supply Voltage	24 V dc

## Mechanical Specifications

Housing Material	ABS
------------------	-----

## Protection Category

IP Rating	IP43
-----------	------

## Operation Environment Specifications

Maximum Operating Temperature	50 °C
Minimum Operating Temperature	-20 °C

## Measurement Specifications

Maximum Sound Level	92 dB
Minimum Sound Level	88 dB

## Approvals

Standards/Approvals	CE, EAC
---------------------	---------