



D-630 to D-655 SLOTTED SCREWDRIVER



Part no.	Tip size	OAL mm	Blade length mm	Blade diameter mmφ	Handle diameter mmφ	Weight g
D-630-75	⌀2.5 × 0.35	124	75 100	3.0	15.4	9
D-630-100		149				10
D-640-100	⌀4.0 × 0.45	178		4.0	19.8	25
D-650-100	⌀5.0 × 0.7	200		5.0	30.0	57
D-655-100	⌀5.5 × 0.8					

▲Warning

- A screwdriver is designed to turn screws, and should not be used for any other purpose.
- Do not use where electrical currents exist.

マイナスドライバー



品 番	先端サイズ mm	全長 mm	軸長 mm	軸径 mmφ	ハンドル径 mmφ	重量 g
D-630-75	φ2.5×0.35	124	75	3.0	15.4	9
D-630-100		149	100			10
D-640-100	φ4.0×0.45	178		4.0	19.8	25
D-650-100	φ5.0×0.7	200		5.0	30.0	57
D-655-100	φ5.5×0.8					
D-240-100	φ4.0×0.45	180	100	4.0	21	35