

Datasheet

RS Pro AC Analogue Panel Voltmeter, 300V, 92 x 92 mm,

RS Stock No: **901-0539**



Product Details

RS Pro analogue panel voltmeter has cut-out dimensions of 92 x 92 mm, is a moving iron for 300 V ac current. It has ABS and polycarbonate enclosure. The operating temperature ranges from -25 to +50°C.

Features and Benefits

- Panel mounting
- Case and terminal protection material UL 94VO
- 1.5 accuracy class

**Specifications:**

Approvals	RoHS Compliant; CE; TUV; UL E327849
Current Type	AC
Meter Type	Moving Iron
Cutout Height	92 mm
Cutout Width	92 mm
Depth	45 mm
Maximum Displayed Value	300 V
Maximum Temperature	+50°C
Measurement Range	0 to 300 V
Minimum Displayed Value	0 V
Minimum Temperature	-25°C
Cutout Size	92 x 92 mm
Meter Accuracy	±1.5%
Dimensions	96 x 96 mm
Enclosure Material	ABS, PC
Mounting Type	Panel Mount