



**3**  
JAHRE  
YEARS  
GARANTIE  
WARRANTY

## ANSMANN HD Headlight HD150BS

- High-quality, multifunctional head lamp made from robust ABS plastic
- With sensor technology – simple to switch on and off with hand-gesture control
- High-quality LED technology with super-bright 5W LED and 5mm LED for optimum illumination
- Optimum lighting thanks to high-efficiency reflector system
- Head light can be individually adjusted with an incline angle up to 45°
- Super-light with flexible, adjustable head band, and so comfortable to wear (just 87g incl. batteries)
- Head band incl. hanging hook and "Thunderer" whistle
- IP54 protection rating (protected from dust and splashed water)
- Three light functions: 100% 5W LED High-power mode | 30% 5W LED Eco mode | 100% 5mm Auxiliary LEDs
- Brightness | Battery life: 150lm | 8.5h (High-power mode), 50lm | 15.5h (Eco mode), 4lm | 30h (Auxiliary LEDs)
- Light range: 5W LED: 70m | Auxiliary LEDs 5mm: 6m
- Incl. 3x AAA alkaline batteries

## INFORMATION

Product name	HD Headlight HD150BS
Part No.	1600-0199
EAN-Code	4013674127559
Customs tariff number	8513100000
Material Group	88
Product content	Head light, head band, 3 AAA alkaline batteries

Product	60 × 53 × 45 mm / 87g
Packing + Product	125 × 50 × 272 mm / 173g
Packing Unit	6 (200 × 135 × 285 mm)

