



Dell B2360dn with optional 550-sheet tray

Great value with essential productivity features.

Designed for small and medium sized businesses and small workgroups, the Dell B2360d and B2360dn Mono Laser Printers offer professional quality double-sided prints, fast print speeds and reliable performance — all at an affordable price.

Featuring a high monthly duty cycle, large onboard memory and high speed processor, these value packed printers help boost office productivity. Match your growing business needs by increasing the input paper capacity with an optional 550-sheet input paper tray*.

For enhanced efficiency, the Dell B2360dn includes built-in Ethernet with fast gigabit network data transfer and security features to help protect data. There is also an option to connect to a wireless network with the optional External Wireless Adaptor*.

Accomplish more and gain outstanding value for your business with the Dell B2360d and B2360dn Mono Laser Printers.

*Optional, sold separately.



Dell™ B2360d and B2360dn Mono Laser Printers



Dell B2360d and B2360dn Mono Laser Printers

Boost office productivity

- Fast printing speed of up to 38 ppm¹ (A4) with up to 1200 x 1200 dpi resolution.
- Powerful 800Mhz dual-core processor and large onboard memory (128MB² for Dell B2360d; 256MB² for Dell B2360dn) enables fast data processing.
- Get fast network data transmission with Gigabit Ethernet 10/100/1000 (applicable for Dell B2360dn only).
- Stay well stocked with the standard 250-sheet paper tray. Or, expand the printing capacity with the optional 550-sheet input paper tray (sold separately).

Reliable performance at an affordable price

- With a maximum duty cycle of up to 80,000 pages per month³, the Dell B2360d and B2360dn printers are able to meet high office printing demands reliably.
- Minimise downtime and maintenance cost with the high page yield imaging drum of up to 60,000 pages.
- Works seamlessly with your new Microsoft® Windows® 8 operating system.

Environmentally-conscious design with security features

- Reduce paper usage by up to 50% with automatic two-sided printing and reduce energy consumption by enabling the Eco Mode function.
- Physically lock your printer with a Kensington Lock. Use the optional lockable paper tray to protect costly or sensitive media, such as company letterheads or checks (Kensington Lock and optional Lockable Tray sold separately).

Do more with Dell B2360dn

- Connect your printer to a wireless network⁴ with the optional External Wireless Adaptor (sold separately).
- Monitor, manage and create reports for the printer fleet on your network with Dell OpenManage™ Printer Manager V2 (OPPM) utility. Use the OPPM to easily update the entire managed printing environment.
- Eliminate the clutter on PCs by replacing multiple print drivers with one versatile solution, the Dell Open Printer Driver (OPD). It is designed to help reduce the huge workload of driver deployment and setting changes.
- Print directly from Android™ mobile devices using Dell Mobile Print app⁵.

Get secured with Dell B2360dn

- Gain peace of mind with security features anchored to protect your data. Dell B2360dn supports SNMPv3 to ensure network security, while the optional External Wireless Adaptor supports WPA2.0 and 802.1X wireless security.
- Securely access the Embedded Web Server (EWS) via password for secure authentication. Valid credentials must be provided before gaining access to the protected function.



Increase efficiency with fast print speeds of up to 38ppm (A4)¹ and automatic two-sided printing.



Intuitive user interface with 2 Line LCD, 7 Buttons, 1 LED indicator.



Increase the printing capacity to 850-sheets by adding an optional 550-sheet tray (sold separately).



Maximise network performance with built-in Gigabit Ethernet 10/100/1000 (Networking capability is applicable to Dell B2360dn only).



Easily connect to a wireless network with the optional External Wireless Adaptor (applicable to Dell B2360dn only).



Print directly from Android™ mobile devices using the **Dell Mobile Print** app⁵ (applicable to Dell B2360dn only).

1. Measured in accordance with ISO IEC 27434/35 methodology. Actual print speeds will vary with use.

2. 1 MB means 1 million bytes, 1 GB means 1,000 megabytes or 1,000,000,000 bytes; total accessible capacity varies depending on operating environment.

3. Duty cycle is defined as the maximum number of imaged outputs a device could deliver in a month. This metric provides a comparison of robustness in relation to other Dell printers and multifunction printers.

4. PC must have a wireless card or be connected to a wireless network and have the printer software installed for proper function.

5. The printer and the mobile device must be connected to the same wireless network.



1. 150-sheet output tray
2. Control panel - 2 Line LCD, 7 buttons, 1 LED
3. 50-sheet multipurpose tray
4. Gigabit Ethernet 10/100/1000 port (rear of printer - applicable to Dell B2360dn only)
5. 250-sheet input tray

Consumables

Ship-with toner cartridge¹
2,500 pages

Standard capacity toner cartridge¹
2,500 pages

High capacity toner cartridge¹
8,500 pages

Imaging drum capacity
60,000 pages

Toner recycling

Free and environmentally responsible toner recycling solutions for all private and business needs. For more information, visit dell.co.uk/recycle.

Accessories

- External Wireless Adaptor (applicable to Dell B2360dn only)
- 550-sheet input paper tray
- 550-sheet lockable input paper tray

Warranty and service options

Standard service

1 Year Next Business Day Service after Remote Diagnosis².

Service upgrade options

- 2 - 5 Years Next Business Day Service after Remote Diagnosis².
- 1 - 5 Years Dell ProSupport™ available during the term of warranty.

Configuration options

■ Standard □ Optional (sold separately)



Standard B2360d or B2360dn configuration:

■ Standard tray	250-sheet
■ Multipurpose tray	50-sheet
Total	300-sheet



Extended B2360d or B2360dn configuration:

■ Standard tray	250-sheet
■ Multipurpose tray	50-sheet
□ 550-sheet tray	550-sheet
Total	850-sheet

Physical specifications

Dimensions (W x D x H)	Printer: 399 mm x 382 mm x 262.7 mm; Shipping: 472 mm x 432 mm x 380 mm
Weight	Printer: 14.1 kg with consumables; Shipping: 15.9 kg
Operating environment	Temperature: 16°C to 32°C; Relative humidity: 8% to 80% RH, non-condensing; Altitude: ≤ 2896 m
Storage environment	Temperature: -40°C to 43.3°C; Relative humidity: 8% to 80% RH, non-condensing; Altitude: ≤ 2896 m
Acoustics	Printing (simplex mode): 54 dBA ³ ; Standby mode: 16 dBA ³

Power specifications

Voltage	230 VAC models: 220 to 240 VAC at 47 to 63 Hz nominal
Power consumption	Ready mode: 8W; Simplex mode: 560W; Duplex mode: 380W Power Saver sleep mode: 5W; Power Saver deep sleep mode: 0.5W; Off mode: 0W
Typical energy consumption	2.08 kWh/week
Environmental compliance	ErP lot 4 and 6, RoHS-compliant ⁷ , ENERGY STAR [®] qualified ⁸ , Blue Angel (Germany), WEEE, CEC/CECP (China)

Supported languages

Chinese - Simplified, Czech, Danish, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Norwegian, Polish, Portuguese Braz., Romanian, Spanish, Swedish, Turkish

1. Toner yield based on testing in accordance with ISO/IEC 19752. Yields vary with usage and environmental conditions.

2. For a copy of Limited Hardware Warranty, write Dell Products, Dell House, The Boulevard, Cain Road, Bracknell, Berkshire, RG12 1LF, UK or see dell.com/warranty. For warranty information for other countries, see website: dell.com/servicecontracts and then select the country. Service may be provided by third party. Technician will be dispatched if necessary following phone-based troubleshooting. Subject to parts availability, geographical restrictions and terms of service contract. Service timing dependent upon time of day call placed to Dell. Defective unit must be returned.

3. Tested in accordance with ISO 7779 and reported in accordance with ISO 9296. Acoustics - Declared noise emission values of computer and business equipment

4. Meets the requirements of the EU Directive on the Restriction of the use of certain Hazardous Substances dated January 27, 2003.

5. For details on energy efficiency of ENERGY STAR[®] qualified products, refer to: www.energystar.gov

Product Specifications		Dell B2360d	Dell B2360dn
Printer specifications	Print speed	Up to 38 ppm (A4) ¹ ; (Actual print speed vary with use)	
	First page out time from Ready state (simplex)	Less than or equals to 6.5 seconds	
	Print resolution	600 X 600 dpi (Default), up to 1200 x 1200 dpi (Max)	
	User interface	2 Line LCD, 7 buttons, 1 LED (Ready, Error)	
	Print language	PCL-XL, PCL5C, PCL5e, PCL 6, PostScript® 3 Emulation, XPS	
	Fonts	8.11H01 (Full Font Load), 2 PCL Bitmapped, 89 PCL Scalable, 91 Postscript® Scalable, 5 PPDS Bitmapped, 39 PPDS Scalable	
	Processor speed/memory	800 MHz / 128 MB ² RAM	800 MHz / 256 MB ² RAM
	Memory expansion	Not available	
	Maximum duty cycle	Up to 80,000 pages per month ³	
	Recommended monthly print volume	750 - 2,500 pages per month	
Mobile printing	Not available	Dell Mobile Print (Android™ OS mobile devices)	
Printer management	Not available	Dell Printer Configuration Web Tool (EWS), Dell OpenManager™ Printer Manager v2	
Connectivity	Interfaces	USB 2.0 High speed	Gigabit Ethernet 10/100/1000, USB 2.0 High-Speed, Wireless 802.11x Option
Operating systems	Windows	Windows® 8, Windows® Server 2008 R2, Windows® Server 2008 R2 SP1, Windows® Server 2008 SP1 6, Windows® Server 2012, Windows® 7, Windows® 7 SP1, Windows® XP SP2, Windows® XP SP3, Windows® Server 2003 SP1, Windows® Server 2003 SP2, Windows® Vista SP1, Windows® Vista SP2	
	Macintosh	Macintosh OS X (10.5, 10.6, 10.7), Macintosh OS X 10.8 (web only, no support on CD)	
	Others	Various Linux including Red hat enterprise, SUSE, Open SUSE, Linspire, Debian, Ubuntu, Fedora, Mint, PC Linux, Linpus, Red flag. SAP® R/3 v4.6C, 4.x and 3.x and later. Novell® Open Enterprise Server and Novell® NetWare® 5.x, 6.x, Various UNIX including HP UX, Sun Solaris, IBM AIX, Various Citrix XenApp support, including the latest Xenapp 6.5 and 6.0. For more information, please view the documents shipped with printer.	
Standard media types, sizes and paper weights	Standard tray		
	Media types supported	Paper Labels, Plain Paper, Transparencies, Bond, Letterhead, Coloured Paper, Custom, Light (Weight should be more than 60 g/m ²), Heavy	
	Media sizes	A4, A5, A6 - only long grain, Executive, Folio, JIS B5, Legal, Letter (US), Statement, Universal	
	Multipurpose tray		
	Media types supported	Card stock, Envelopes (smooth), Paper Labels, Plain Paper, Polyester Labels, Transparencies, Bond, Letterhead, Coloured Paper, Custom, Light (Weight should be more than 60 g/m ²), Heavy	
	Media sizes	A4, A5, A6 - only long grain, Executive, Folio, JIS B5, Legal, Letter (US), Statement, Universal, DL Envelope, 7 3/4 Envelope (Monarch), Universal, 10 Envelope, Other Envelope: 98.4 mm x 162 mm to 176 mm x 250 mm	
Page layout options	Portrait, Landscape, Multiple copies, Duplex printing, Multipage printing (N-up-Max 16), Poster, Booklet, Watermarks, Collate, Reverse Page Order, Rotate 180, Mirror		
Paper handling	Standard input sources	250-sheet standard tray, 50-sheet multipurpose tray	
	Optional input capacity	550-sheet input tray	
	Maximum input capacity	850-sheet	
	Duplexer	Automatic	
	Standard output destination	150-sheet	
	Maximum output capacity	150-sheet	
Product certifications	Safety certifications	IEC60950/EN60950/UL60950; IEC60825-1/EN 60825-1:2007 (Laser); CE Mark (EU); NEMKO (Nordic); GS Mark (Germany); UL/cUL Listed (UL60950-1 US/Canada); FDA/DHHS (21CFR, Chapter 1, Subchapter J, Class-1 Laser, US); NOM (Mexico); CCC (China); VCCI Class B (Japan), other safety approvals required by individual countries	
	Other certifications	EN55022:2006 + A1:2007 Class B, EN61000-3-2:2006 + A1:2009 + A2:2009, EN61000-3-3:2008, EN55024:1998 + A1:2001 + A2:2003, FCC CFR Title 47, Part 15 Class B (USA); ICES-003, Issue 4 (Canada); and other certifications required by individual countries.	
Contents in box	Dell B2360d or B2360dn Mono Laser Printer, Ship-With 2,500-page yield ⁴ Black Cartridge, Power cord, Quick Setup Sheet, Software and Instructions CD, Use and Return Sheet, Product Information Guide, Blue Angel Tech Sheet (Europe only), European Voluntary Agreement Information Sheet (Europe and TAA 220v only)		

1. Measured in accordance with ISO IEC 27434/35 methodology. Actual print speeds will vary with use.

2. 1 MB means 1 million bytes, 1 GB means 1,000 megabytes or 1,000,000,000 bytes; total accessible capacity varies depending on operating environment

3. Duty cycle is defined as the maximum number of imaged outputs a device could deliver in a month. This metric provides a comparison of robustness in relation to other Dell printers and multifunction printers.

4. Toner yield based on testing in accordance with ISO/IEC 19752. Yields vary with usage and environmental conditions.

©2014 Dell Corporation Limited. Dell, the Dell logo and Dell Toner Management System are registered trademarks or trademarks of Dell Inc. Other trademarks and trade names may be used in this document to refer to either the entities claiming the marks and names or their products. Dell disclaims proprietary interest in the marks and names of others. Microsoft, Windows and Windows NT are registered trademarks or trademarks of Microsoft Corporation. Dell Products, Dell House, The Boulevard, Cain Road, Bracknell, Berkshire, RG12 1LF, UK.

Product availability varies by country. Please contact your Dell representative for more information.

Specifications are subject to change without notice. Dell cannot be responsible for errors and omissions in typography or photography.

G120036078 - B2360d and B2360dn