

Wall mounted receptacle  
Part no. 7624




- screwless spring terminals
- for horizontal installation
- switched
- mechanical DUO-interlock
- receptacles can be padlocked

Technical specifications

|                       |                         |
|-----------------------|-------------------------|
| Ampere                | 16 A                    |
| Poles                 | 4 p                     |
| Voltage               | 400 V                   |
| Clock position        | 6 h                     |
| Hertz                 | 50-60 Hz                |
| Connection technology | Screwless - TwinCONTACT |
| Contact               | standard                |
| Protection type       | IP67                    |
| Enclosure material    | Plastic                 |
| Weight                | 1340 g                  |

Drawing



| Drawing<br>1 MB 551<br>Dim. in mm | Amp.<br>Poles | 16  |     |     | 32  |     |     |
|-----------------------------------|---------------|-----|-----|-----|-----|-----|-----|
|                                   |               | 3   | 4   | 5   | 3   | 4   | 5   |
| a                                 |               | 225 | 225 | 225 | 225 | 225 | 225 |
| b                                 |               | 168 | 168 | 168 | 168 | 168 | 168 |
| b1                                |               | 130 | 130 | 130 | 130 | 130 | 130 |
| c                                 |               | 80  | 80  | 80  | 80  | 80  | 80  |
| c1                                |               | 166 | 166 | 166 | 166 | 166 | 166 |
| c2                                |               | 182 | 185 | 186 | 197 | 197 | 198 |
| d                                 |               | 204 | 204 | 204 | 204 | 204 | 204 |
| d1                                |               | 145 | 145 | 145 | 145 | 145 | 145 |
| e                                 |               | 150 | 150 | 150 | 150 | 150 | 150 |
| f                                 |               | 7   | 7   | 7   | 7   | 7   | 7   |
| f1                                |               | Ø7  | Ø7  | Ø7  | Ø7  | Ø7  | Ø7  |
| g                                 |               | 8   | 8   | 8   | 8   | 8   | 8   |