

Spec. Cable Gland M32 Cable-Ø13-21 SBC



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5014
Specification	Spec. Cable Gland M32 Cable-Ø13-21 SBC
HARTING eCatalogue	https://harting.com/19000005014

Identification

Category	Accessories
Series of hoods/housings	Han® HPR EasyCon
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Tightening torque	20 Nm
Wrench size	36
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65 / IP68
Size	M32
Clamping range	13 ... 21 mm
Width across corners	40 mm

Material properties

Material (cable glands)	Brass
Material (seal)	EPDM
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	134.163 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140123564
eCl@ss	27140803 Cable gland EMC (electrical installation)
ETIM	EC000441
UNSPSC 24.0	39121431