

216EP9

Industrial Plug

2CMA101948R1000

Industrial Plugs, 2P+E, 16A, 380 ... 415 V Clock Position Of
Grounding Contact 9 hour Color code Red



GENERAL

Product Name	Industrial Plug
Product ID	2CMA101948R1000
Function	Plug
EAN	73926919484
Catalog Description	Industrial Plugs, 2P+E, 16A, 380 ... 415 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	E2416162
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EP
Color	Red
Number of Poles	3
Clock Position	9Hour
Rated Current	16 ampere
Rated Voltage	380 ... 415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1...2.5 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	57 millimetre
Product Net Height	63 millimetre
Product Net Length	127 millimetre
Product Net Depth	127 millimetre
Product Net Weight	0.11 kilogram

PACKAGING

Package Width	120 millimetre
Package Height	285 millimetre
Package Gross Weight	1.1 kilogram
Package Length	138 millimetre
Package Units	box 10 piece