


datasheet for VON 20
article number: 930046103



product description:	order number: 930 046-103
description:	Fully mating connector ,shatter-proof, flexible insulated sleeve. The tapering sleeve end also serves as kinking protection for the lead. Screw connection up to maximum cable cross-section of 1.5 mm ² . Nickel-plated brass contact material.
typ:	VON 20 gelb/yellow
system:	4 mm system
order number:	930 046-103
color	
other color versions:	
technical data	
pin dimensions	4 mm
type of contact:	spring loaded pin
type of termination:	screw
rated voltage:	DC 60 V
rated current:	16 A
contact resistance:	3 mOhm
material	
contact material:	brass
contact surface material:	nickel-plated
housing material:	PVC-P
environmental conditions:	
temperature range:	-25 °C to +70 °C
inflammable class:	
housing:	94 V-2
drawing	

