





EPK105-120KC

Battery operated cutting tool 120 kN with scissor head, 105 mm capacity.

Scissor type cut offering easy access.
Ergonomic handle and triggers to Allow its manoeuvrability with gloves.
Tool perfectly balanced to ensure a maximum comfort.



 F kN	 Ø mm	 mm	 kg
120	105	618 x 495 x 102	11.0

Characteristics:

- **Ergonomic design:** optimizing the position of centre of gravity.
- **Cutting capacity:** Cu, Al, light weight armoured Cu/Al, armoured Cu/Al cables 105 mm diameter.
- **Head rotation:** 350°.
- **Data display:**
 - OLED technology
 - Cumulative working cycles
 - Battery status maintenance notification
 - Fault codes
- **Retraction:** automatic after cutting completion.
- **Mechanism:** two-stage hydraulic system with fast-feed and power-control.
- **Assistance:** LED to illuminate the cut area.
- **Maintenance:** please contact your nearest Sicame Group Service Center.
 - Replacement of cutting blades
 - Periodic maintenance: 20 000 cycles.

• **Kit content:**

- Battery operated tool
- Two 18 V 5,0 Ah batteries
- Fast charger
- Thermoplastic carrying case (dimensions: 715 x 505 x 160 mm)
- Total kit weight: 18,7 kg



EPK-105120-KC



DC-18RC



BL1850B