



PRODUCT-DETAILS

# SGP-29

## SYSTEM SUPPORT PA6 NW29 GRY



---

### General Information

Extended Product Type	SGP-29
Product ID	7TCA292000R6640
EAN	7630031201928
Catalog Description	SYSTEM SUPPORT PA6 NW29 GRY
Long Description	Stackable Support for Conduit, Fits NW 29 with Both Fine and Course Profiles, Grey

---

### Additional Information

Application	Railway Vehicle Construction, Heavy Machine Building, Other Applications with Increased Mechanical Requirements
Product Type	Flexible Conduit Support Systems

---

### Ordering

EAN	7630031201928
UPC	786210057958

---

## Dimensions

---

Thickness	36 mm
-----------	-------

---



---

## Technical

---

Number of Batteries	0
Color	Gray
Material	High-Grade Specially Formulated Polyamide/Nylon 6

---



---

## Environmental

---

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

---



---

## Container Information

---

Package Level 1 Units	80 EA
Package Level 1 Height	219.989 mm 8.661 in
Package Level 1 Depth / Length	399.999 mm 15.748 in
Package Level 1 Width	299.999 mm 11.811 in

---



---

## Certificates and Declarations

---

Data Sheet, Technical Information	SGP-29
Instructions and Manuals	SGP-29
Declaration of Conformity - CE	9AKK107680A0674

---



---

## External Classifications and Standards

---

ETIM 8	EC000368 - Tube clamp
UNSPSC	39121701

---



---

## Categories

---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

