

Blower LXT®

DUB187

18V, 64 m/s

Model DUB187 is a cordless blower powered by 18V LXT Li-ion battery.

The main features and benefits are: Variable speed control by trigger plus Cruise control, Single action lever for blower/vacuum mode selection, Dust bag with a large inlet opening, Two casters.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Brushless Motor	✓
No load speed	9 000 - 13 500 min ⁻¹
Max. Air Velocity	64 m/s
Blowing force	4,2 N
Air volume	4,2 m ³ /min
Continuous Use 18V / 6.0 Ah Battery	14 min
Sound Power Level (L _{WA})	94,32 dB(A)
Sound Pressure Level (L _{pA})	82 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,7 - 4,0 kg
Product Dimensions (L x W x H):	1168 x 164 x 416 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion

User benefits

- Lock-on feature for continuous operation
- Soft grip handle provides increased comfort on the job
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing