



40VMax Chainsaw XGT®

UC022G

350 mm, 80TXL

This model is a cordless rear-handle chain saw powered by 40Vmax XGT Li-Ion battery

Achieving cutting performance and weight equivalent to the superior 35mL class engine chainsaw. Also features new Tool-less change and tension adjustment of saw chain as well as excellent acceleration.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Chain Speed (No Load)	25,5 m/s
chain bar length	350 mm (14")
Chain Pitch	0,325 "
Chain Gauge	0,043 "
Chain Gauge	1,1 mm
Number of Drive Links	59
Chain Oil Tank	200 ml
Brushless Motor	✓
Vibration Level, Cutting Wood	3,5 m/s ²
Vibration Uncertainty (K Factor), Cutting Wood	1,5 m/s ²
Sound Pressure Level (L _{pA})	93 dB(A)
Sound Power Level (L _{WA})	101 dB(A)

User benefits

- Adjustable automatic chain lubrication with large oil reservoir
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Lightweight & high power

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing