

Miniature twin round screened cable



Part NO: RGW-1650
Product Code: Miniature twin round screened cable
Product Description

Application:
 For communication and signal control systems.
Reference Standard
 Customer's sample spec.and the general standard

Multi-construction
 2

Cable Construction

Conductor	Bare Copper
Construction	0.20±0.003x7
Stranded Dia.(±0.01mm)	0.60
Insulation	PVC
Thickness	0.5
Insulation Dia.(±0.1mm)	1.60
Insulation Color	Red; Blue
Filler	Cotton yarn
Braiding	Bare Copper
Construction (mm)	0.10±0.003×16×6
coverage	≥81%
Jacket	PVC
Thickness(mm)	≥0.65
Dia.(±0.2mm)	5.15
Jacket Color	Grey(RAL7001)

Marking
 Miniature twin round screened cable ww/yy +Meter marking


PACKAGING
 100m/Reel 25M/Reel

RoHS GUIDELINE			
We operate according to the following standards			
Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls(PBB)	Forbidden	GC/MS	
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	

Revision History

A0-1

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω/Km)	84.6
Min.Insulation DC Resistance at 20°C (MΩ *Km)	>500
Rated Temperature(°C)	-20 to +60
Rated Voltage(V)	30

Label on Reel

Product label

Miniature twin round screened cable

Grey
100M
RoHS(2002/95/EC) Compliant
WW/YY

RS label

7492591
 100M
 Made in China

7492579
 25M
 Made in China

Date: 2011-09-13

Page: 1 / 1