



PRODUCT-DETAILS

PACS34/BL/50M**34MM PA6 CONDUIT 50M - BL****General Information**

Extended Product Type:	PACS34/BL/50M
Product ID:	7TCA296000R2004
EAN:	5020963003790
Catalog Description:	34MM PA6 CONDUIT 50M - BL
Long Description:	Standard Weight Conduit, Nominal Conduit Size 34mm, NW Conduit Size 29, Coarse Conduit Pitch, Outside Diameter 34.5mm, Inside Diameter 27.7mm, Static Bend Radius 60mm, Reel Length 50 Meters, Polyamide (Nylon) 6, Black
Display Name:	PACS34/BL/50M

Eco Transparency

Environmental Product Declaration - EPD: 9AKK108469A9306

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Indoors / Outdoors - Light Industrial, Buildings & Machinery

Ordering

EAN:	5020963003790
UPC:	786210267630

Dimensions

Outside Diameter:	34.5 mm
--------------------------	---------

Technical

Number of Batteries:	0
Color:	Black
Material:	Polyamide/Nylon 6

Environmental

WEEE Category:	Product Not in WEEE Scope
RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units:	1 piece
Package Level 1 EAN:	5020963003790
Package Level 1 Height:	7.87 in 200 mm
Package Level 1 Depth / Length:	29.53 in 750 mm
Package Level 1 Width:	29.53 in 750 mm

Certificates and Declarations

Declaration of Conformity - CE:	9AKK107492A9618
RoHS Declaration:	9AKK107992A8994
REACH Declaration:	9AKK107992A8994

External Classifications and Standards

ETIM 8:	EC001175 - Corrugated plastic hose
ETIM 9:	EC001175 - Corrugated plastic hose

UNSPSC:

39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

